

分光模块&手动衰减器


- 结构紧凑，稳定，透反比例可调
- 熔融石英材料
- 大入射孔径，3种安装方式
- 匹配专用滑台，可方便XY调节




常规型号

	波长	最大入射光斑	损伤阈值	衰减比例	型号
分光模块	355nm	12mm	4,5 J/cm ² at 10 ns, 10 Hz, 355 nm	图一	EMC-PS-355-10
	532nm	12mm	6 J/cm ² at 10 ns, 10 Hz, 532 nm	图一	EMC-PS-532-10
	1064nm	12mm	10 J/cm ² at 10 ns, 10 Hz, 1064nm4,	图一	EMC-PS-1064-10
手动衰减器	355nm	12mm	5 J/cm ² at 10 ns, 10 Hz, 355 nm	图二	EMC-PS-355-10S
	532nm	12mm	6 J/cm ² at 10 ns, 10 Hz, 532 nm	图二	EMC-PS-532-10S
	1064nm	12mm	10 J/cm ² at 10 ns, 10 Hz, 1064nm	图二	EMC-PS-1064-10S


注：1. 分光平片可选择采用分光晶体
 2. 可选配二维滑台及收光筒



分光模块&手动衰减器



(图一) 分光模块



(图二) 手动衰减器